



AREA	CABINA	SB	NOME SB	NR STR.	LUNG.	NR cavi	SEZ
1	C01	01	SB-10001	7	230	1	150
1	C01	02	SB-10002	8	270	1	150
1	C01	03	SB-10003	11	250	1	185
1	C01	04	SB-10004	11	240	1	185
1	C01	05	SB-10005	11	230	1	185
1	C01	06	SB-10006	11	210	1	150
1	C01	07	SB-10007	12	200	1	185
1	C01	08	SB-10008	12	190	1	150
1	C01	09	SB-10009	14	180	1	185
1	C01	10	SB-10010	14	180	1	185
1	C01	11	SB-10011	16	170	1	185
1	C01	12	SB-10012	16	190	1	240
1	C01	13	SB-10013	14	200	1	185
1	C01	14	SB-10014	12	60	1	150
1	C01	15	SB-10015	16	70	1	185
1	C01	16	SB-10016	16	80	1	185
1	C01	17	SB-10017	16	100	1	185
1	C02	01	SB-10201	10	230	1	150
1	C02	02	SB-10202	12	220	1	185
1	C02	03	SB-10203	12	210	1	185
1	C02	04	SB-10204	12	200	1	185
1	C02	05	SB-10205	14	190	1	185
1	C02	06	SB-10206	14	180	1	185
1	C02	07	SB-10207	16	170	1	185
1	C02	08	SB-10208	16	180	1	185
1	C02	09	SB-10209	16	190	1	240
1	C02	10	SB-10210	14	210	1	240
1	C02	11	SB-10211	14	220	1	240
1	C02	12	SB-10212	11	230	1	185
1	C02	13	SB-10213	12	140	1	150
1	C02	14	SB-10214	12	130	1	150
1	C02	15	SB-10215	15	80	1	185
1	C02	16	SB-10216	16	120	1	185
1	C03	01	SB-10301	18	130	1	240
1	C03	02	SB-10302	18	90	1	240
1	C03	03	SB-10303	15	70	1	185
1	C03	04	SB-10304	16	60	1	185
1	C03	05	SB-10305	14	70	1	185
1	C03	06	SB-10306	11	190	1	150
1	C03	07	SB-10307	11	200	1	150
1	C03	08	SB-10308	11	210	1	150
1	C03	09	SB-10309	11	230	1	185
1	C03	10	SB-10310	11	250	1	185
1	C03	11	SB-10311	10	280	1	185
1	C03	12	SB-10312	10	340	1	240
2	C04	01	SB-20401	14	160	1	185
2	C04	02	SB-20402	16	130	1	185
2	C04	03	SB-20403	16	110	1	185
2	C04	04	SB-20404	16	100	1	185
2	C04	05	SB-20405	14	120	1	185
2	C04	06	SB-20406	14	140	1	185
2	C04	07	SB-20407	12	160	1	150
2	C04	08	SB-20408	16	40	1	185
2	C04	09	SB-20409	15	90	1	185
2	C04	10	SB-20410	12	130	1	150
2	C04	11	SB-20411	11	140	1	120
2	C05	01	SB-20501	16	120	1	185
2	C05	02	SB-20502	16	110	1	185
2	C05	03	SB-20503	16	100	1	185
2	C05	04	SB-20504	15	110	1	185
2	C05	05	SB-20505	15	100	1	185
2	C05	06	SB-20506	14	180	1	185
2	C05	07	SB-20507	15	170	1	185
2	C05	08	SB-20508	15	150	1	185
2	C05	09	SB-20509	16	130	1	185
2	C05	10	SB-20510	16	120	1	185
2	C05	11	SB-20511	15	130	1	185
2	C05	12	SB-20512	15	150	1	185
2	C05	13	SB-20513	15	160	1	185
2	C05	14	SB-20514	14	180	1	185
2	C05	15	SB-20515	14	200	1	185
2	C05	16	SB-20516	13	220	1	185
3	C06	01	SB-30601	10	130	1	120
3	C06	02	SB-30602	12	90	1	150
3	C06	03	SB-30603	16	30	1	185
3	C06	04	SB-30604	15	40	1	185
3	C06	05	SB-30605	15	80	1	185
3	C06	06	SB-30606	14	110	1	185
3	C06	07	SB-30607	16	110	1	185
3	C06	08	SB-30608	15	110	1	185
3	C06	09	SB-30609	16	110	1	185
3	C06	10	SB-30610	16	120	1	185
3	C06	11	SB-30611	16	140	1	185
3	C07	01	SB-30701	14	100	1	185
3	C07	02	SB-30702	14	80	1	185
3	C07	03	SB-30703	15	30	1	185
3	C07	04	SB-30704	12	70	1	150
3	C07	05	SB-30705	16	170	1	185
3	C07	06	SB-30706	16	150	1	185
3	C07	07	SB-30707	15	130	1	185
3	C07	08	SB-30708	16	110	1	185
3	C07	09	SB-30709	16	130	1	185
3	C07	10	SB-30710	14	140	1	185
3	C07	11	SB-30711	12	160	1	150

Individuazione string box

AREA IMPIANTO NR. POWER STATION
 "STRING BOX" NR. STRING BOX

AREA	CABINA	SB	NOME SB	NR STR.	LUNG.	NR cavi	SEZ
3	C08	01	SB-30801	14	140	1	185
3	C08	02	SB-30802	14	130	1	185
3	C08	03	SB-30803	16	120	1	185
3	C08	04	SB-30804	16	100	1	185
3	C08	05	SB-30805	16	90	1	185
3	C08	06	SB-30806	16	110	1	185
3	C08	07	SB-30807	14	130	1	185
3	C08	08	SB-30808	11	140	1	120
3	C08	09	SB-30809	12	160	1	185
3	C08	10	SB-30810	16	140	1	185
3	C08	11	SB-30811	16	120	1	185
3	C08	12	SB-30812	16	100	1	185
3	C08	13	SB-30813	16	100	1	185
3	C08	14	SB-30814	16	120	1	185
3	C08	15	SB-30815	10	140	1	120
3	C08	16	SB-30816	10	150	1	120
3	C09	01	SB-30901	13	160	1	150
3	C09	02	SB-30902	15	160	1	185
3	C09	03	SB-30903	16	150	1	185
3	C09	04	SB-30904	15	130	1	185
3	C09	05	SB-30905	16	180	1	185
3	C09	06	SB-30906	15	190	1	185
3	C09	07	SB-30907	11	110	1	185
3	C09	08	SB-30908	10	140	1	120
3	C09	09	SB-30909	16	100	1	185
3	C09	10	SB-30910	16	100	1	185
3	C09	11	SB-30911	16	120	1	185
3	C09	12	SB-30912	14	140	1	185
3	C09	13	SB-30913	14	160	1	185
3	C09	14	SB-30914	12	180	1	185
3	C09	15	SB-30915	12	190	1	185
3	C09	16	SB-30916	10	200	1	185
3	C09	17	SB-30917	9	220	1	185
4	C10	01	SB-41001	15	130	1	185
4	C10	02	SB-41002	16	90	1	185
4	C10	03	SB-41003	15	50	1	185
4	C10	04	SB-41004	16	90	1	185
4	C10	05	SB-41005	16	110	1	240
4	C10	06	SB-41006	14	130	1	185
4	C10	07	SB-41007	12	150	1	185
4	C10	08	SB-41008	12	170	1	185
4	C10	09	SB-41009	16	100	1	185
4	C10	10	SB-41010	16	80	1	185
4	C10	11	SB-41011	16	120	1	185
4	C10	12	SB-41012	14	130	1	185
4	C10	13	SB-41013	14	130	1	185
4	C10	14	SB-41014	12	140	1	150
4	C10	15	SB-41015	10	150	1	185
4	C11	01	SB-41101	16	100	1	185
4	C11	02	SB-41102	16	100	1	185
4	C11	03	SB-41103	14	120	1	185
4	C11	04	SB-41104	14	140	1	185
4	C11	05	SB-41105	14	150	1	185
4	C11	06	SB-41106	11	160	1	185
4	C11	07	SB-41107	16	170	1	185
4	C11	08	SB-41108	16	170	1	185
4	C11	09	SB-41109	16	180	1	185
4	C11	10	SB-41110	14	190	1	185
4	C11	11	SB-41111	14	190	1	185
4	C11	12	SB-41112	13	200	1	185
4	C11	13	SB-41113	12	200	1	185
4	C11	14	SB-41114	11	220	1	185
4	C11	15	SB-41115	8	230	1	185
4	C11	16	SB-41116	7	240	1	185
5	C12	01	SB-51201	11	180	1	150
5	C12	02	SB-51202	11	160	1	150
5	C12	03	SB-51203	12	140	1	150
5	C12	04	SB-51204	14	120	1	185
5	C12	05	SB-51205	16	100	1	185
5	C12	06	SB-51206	15	100	1	185
5	C12	07	SB-51207	15	100	1	185
5	C12	08	SB-51208	16	120	1	185
5	C12	09	SB-51209	15	130	1	185
5	C12	10	SB-51210	16	160	1	185
6	C12	11	SB-51211	10	250	1	185
6	C12	12	SB-51212	9	230	1	185
6	C13	01	SB-61301	16	120	1	185
6	C13	02	SB-61302	16	120	1	185
6	C13	03	SB-61303	15	140	1	185
6	C13	04	SB-61304	14	150	1	185
6	C13	05	SB-61305	15	170	1	185
6	C13	06	SB-61306	14	190	1	185
6	C13	07	SB-61307	14	210	1	240
6	C13	08	SB-61308	13	220	1	185
6	C13	09	SB-61309	14	230	1	240
6	C13	10	SB-61310	12	240	1	185
6	C13	11	SB-61311	13	260	1	